

# Synthesis and characterization of mesoporous silver/SBA15 catalyst for the organic synthesis

Boughedir nadia<sup>1,2:3</sup> Bailiche nadia<sup>1,2:3</sup>

<sup>1</sup>Laboratory of catalysis and synthesis in organic chemistry, university of Tlemcen, BP 119, 13000, Algeria.

<sup>2</sup> University of Ain Temouchent, 46000, Algeria.

<sup>3</sup>Laboratory of Applied chemistry, University of Ain Temouchent, 46000, Algeria

\*Correspondingauthor e-mail: boughedirnadia95@gmail.com

### INTRODUCTION

The Ag/SBA15 material was prepared by the incipient wetness impregnation method. The material was characterized by XRD, UV-Vis, BET, IR and Raman microscopies. Ag-SBA15 materials are of purely silver composition with no catalytically active sites inside the pores and on the surface of mesoporous materials which makes it possible to enhance the acid-base properties in order to synthesize Ag-type catalysts /SBA-15 for use in esterification the production of biodiesel.


#### **EXPERIMENTAL**

#### preparation of Ag/SBA15

Preparation of Ag/SBA-15 catalysts by route ."post-synthesis" Ag/SBA15 materials are prepared by the incipient wetness impregnation method. For this, a quantity of calcined SBA15 material is used and mixed with a volume bidistilled water containing an adequate amount of silver nitrate, in a stirrer magnetic heating in order to respectively obtain the Si/Ag ratio =10

## **Catalytic test**

we tested our synthesized materials as catalysts in esterification reactions of acid which is a natural molecule of the fatty acid family.



#### **CHARACTERIZATION OF CATALYSTS**




Fig. 3. FT-IR spectra of SBA-15 and Ag/SBA-15 nanocomposites.




Fig.4..X-RAY Diffraction analysis weak of Ag/SBA15

**CONCLUSIONS** 

The mesoporous The Ag/SBA-15 material was successfully prepared by a post-synthesis method Compound Ag/silica have high surface area and large Structure. Porous volume The results show that: The introduction of silver into SBA-15 mesoporous materials with different Ag ratios leads to the mesoscopic